

Minicylinders - Series 16 - 23 - 24 - 25

Product code: 16N2A10A020V

Datasheet creation date: 07/03/2025 17:55

Check the most updated document online [click here](#)



TECHNICAL DATA

| | |
|---------------------------|----------------------------------------------------------|
| Series (mm) | 16 |
| Bore (mm) | 10 |
| Version | N = standard |
| Operation | 2 = double acting |
| Materials | A = rolled stainless steel stem - stainless steel jacket |
| Construction | A = ring nut V + stem nut U |
| Stroke type | variable |
| Stroke (mm) | 20 |
| Rod seals material | V = FKM rod seal |
| Extended rod (mm) | 0 |

Minicylinders - Series 16 - 23 - 24 - 25

Product code: 16N2A10A020V



DIMENSIONS

| | |
|----------|----------|
| EW (mm) | 8 |
| KW (mm) | 7 |
| BE | M12x1,25 |
| KK | M4x0.7 |
| ØCD (mm) | 4 |
| D1 (mm) | 11.3 |
| EE | M5 |
| ØD2 (mm) | 4 |
| L1 (mm) | 106.0 |
| XC (mm) | 84 |
| L2 (mm) | 66.0 |
| AM (mm) | 12 |
| L3 (mm) | 10 |
| L4 (mm) | 4.5 |
| L5 (mm) | 12 |
| L (mm) | 6 |
| WF (mm) | 16 |
| L6 (mm) | 9 |
| L7 (mm) | 28 |
| KV (mm) | 19 |
| SW (mm) | - |
| D (mm) | 15.0 |
| D3 (mm) | 15 |