

## Minicylinders - Series 16 - 23 - 24 - 25

Product code: 16N2A10A100

Datasheet creation date: 20/05/2026 08:21

Check the most updated document online [click here](#)



### TECHNICAL DATA

<b>Series (mm)</b>	16
<b>Diameter (mm)</b>	10
<b>Version</b>	N = standard
<b>Operation</b>	2 = double acting
<b>Materials</b>	A = rolled stainless steel stem - stainless steel jacket
<b>Construction</b>	A = ring nut V + rod nut U
<b>Stroke (mm)</b>	100
<b>Seal options</b>	= standard
<b>Rod length (mm)</b>	0

## Minicylinders - Series 16 - 23 - 24 - 25

Product code: 16N2A10A100



### DIMENSIONS

EW (mm)	8
KW (mm)	7
BE	M12x1,25
KK	M4x0.7
ØCD (mm)	4
D1 (mm)	11.3
EE	M5
ØD2 (mm)	4
L1 (mm)	186.0
XC (mm)	164
L2 (mm)	146.0
AM (mm)	12
L3 (mm)	10
L4 (mm)	4.5
L5 (mm)	12
L (mm)	6
WF (mm)	16
L6 (mm)	9
L7 (mm)	28
KV (mm)	19
SW (mm)	-
D (mm)	15.0
D3 (mm)	15