

## Minicylinders - Series 16 - 23 - 24 - 25

Product code: 24N2A16A045

Datasheet creation date: 07/03/2025 18:07

Check the most updated document online [click here](#)




### TECHNICAL DATA

|                           |  |
|---------------------------|--|
| <b>Series (mm)</b>        | 24   |
| <b>Bore (mm)</b>          | 16   |
| <b>Version</b>            | N = standard   |
| <b>Operation</b>          | 2 = double acting  |
| <b>Materials</b>          | A = rolled stainless steel stem - stainless steel jacket |
| <b>Construction</b>       | A = ring nut V + stem nut U                              |
| <b>Stroke type</b>        | variable   |
| <b>Stroke (mm)</b>        | 45   |
| <b>Rod seals material</b> | = standard   |
| <b>Extended rod (mm)</b>  | 0  |

## Minicylinders - Series 16 - 23 - 24 - 25

Product code: 24N2A16A045



### DIMENSIONS

|          |         |
|----------|---------|
| EW (mm)  | 12      |
| KW (mm)  | 8       |
| BE       | M16x1,5 |
| KK       | M6x1    |
| ØCD (mm) | 6       |
| D1 (mm)  | 18.0    |
| EE       | M5      |
| ØD2 (mm) | 6       |
| L1 (mm)  | 156.0   |
| XC (mm)  | 127     |
| L2 (mm)  | 101.0   |
| AM (mm)  | 16      |
| L3 (mm)  | 15      |
| L4 (mm)  | 4.0     |
| L5 (mm)  | 17      |
| L (mm)   | 9       |
| WF (mm)  | 22      |
| L6 (mm)  | 10      |
| L7 (mm)  | 38      |
| KV (mm)  | 24      |
| SW (mm)  | 5       |
| D (mm)   | 20.5    |
| D3 (mm)  | 20      |