

Round cylinders - Series 27

Product code: 27M2A20A0200

Datasheet creation date: 07/03/2025 18:58

Check the most updated document online [click here](#)



TECHNICAL DATA

| | |
|----------------------|-------------------------------------|
| Series | 27 |
| Diameter (mm) | 20 |
| Version | M = rear end block upper round part |
| Operation | 2 = double - acting |
| Materials | A = rolled stainless steel |
| Construction | A = standard |
| Stroke type | standard |
| Stroke (mm) | 200 |

Round cylinders - Series 27

Product code: 27M2A20A0200



DIMENSIONS

| | |
|-----------|---------|
| AM (mm) | 14 |
| Ø B (mm) | 16 |
| BF (mm) | 12 |
| BE | M16x1.5 |
| Ø CD (mm) | 6 |
| Ø D (mm) | 21.5 |
| EE | G1/8 |
| EW (mm) | 12 |
| G (mm) | 15.5 |
| G1 (mm) | 8.0 |
| KK | M8x1.25 |
| L (mm) | 7 |
| Ø MM (mm) | 8 |
| L5 (mm) | 13 |
| L6 (mm) | 0 |
| PL (mm) | 9 |
| SW (mm) | 7 |
| VD (mm) | 3 |
| WF (mm) | 17.0 |
| XC (mm) | 77.0 |
| XC1 (mm) | 62.5 |
| XC2 (mm) | 70.8 |
| SW1 (mm) | 19 |

| | |
|------------|-----|
| BG (mm) | 0 |
| BG1 (mm) | 0.0 |
| FB | 0 |
| RT | 0 |
| Ø RT1 (mm) | 0 |
| TC (mm) | 0 |
| TF (mm) | 0.0 |