

Round cylinders - Series 27

Product code: 27M2A40A0260

Datasheet creation date: 07/03/2025 19:07

Check the most updated document online [click here](#)



TECHNICAL DATA

| | |
|----------------------|-------------------------------------|
| Series | 27 |
| Diameter (mm) | 40 |
| Version | M = rear end block upper round part |
| Operation | 2 = double - acting |
| Materials | A = rolled stainless steel |
| Construction | A = standard |
| Stroke type | variable |
| Stroke (mm) | 260 |

Round cylinders - Series 27

Product code: 27M2A40A0260



DIMENSIONS

| | |
|-----------|----------|
| AM (mm) | 23 |
| Ø B (mm) | 30 |
| BF (mm) | 15 |
| BE | M30x1.5 |
| Ø CD (mm) | 10 |
| Ø D (mm) | 41.5 |
| EE | G1/8 |
| EW (mm) | 20 |
| G (mm) | 18.0 |
| G1 (mm) | 5.5 |
| KK | M12x1.25 |
| L (mm) | 5 |
| Ø MM (mm) | 16 |
| L5 (mm) | 15 |
| L6 (mm) | 24 |
| PL (mm) | 10 |
| SW (mm) | 13 |
| VD (mm) | 3 |
| WF (mm) | 24.0 |
| XC (mm) | 96.0 |
| XC1 (mm) | 78.5 |
| XC2 (mm) | 91.0 |
| SW1 (mm) | 38 |

| | |
|------------|-----|
| BG (mm) | 0 |
| BG1 (mm) | 0.0 |
| FB | 0 |
| RT | 0 |
| Ø RT1 (mm) | 0 |
| TC (mm) | 0 |
| TF (mm) | 0.0 |