

## Round cylinders - Series 27

Product code: 27U2A20A0060

Datasheet creation date: 07/03/2025 19:13

Check the most updated document online [click here](#)



### TECHNICAL DATA

|                      |                                     |
|----------------------|-------------------------------------|
| <b>Series</b>        | 27                                  |
| <b>Diameter (mm)</b> | 20                                  |
| <b>Version</b>       | U = rear end block upper round part |
| <b>Operation</b>     | 2 = double - acting                 |
| <b>Materials</b>     | A = rolled stainless steel          |
| <b>Construction</b>  | A = standard                        |
| <b>Stroke type</b>   | variable                            |
| <b>Stroke (mm)</b>   | 60                                  |

## Round cylinders - Series 27

Product code: 27U2A20A0060



### DIMENSIONS

|           |         |
|-----------|---------|
| AM (mm)   | 14      |
| Ø B (mm)  | 16      |
| BF (mm)   | 12      |
| BE        | M16x1.5 |
| Ø CD (mm) | 6       |
| Ø D (mm)  | 21.5    |
| EE        | G1/8    |
| EW (mm)   | 12      |
| G (mm)    | 15.5    |
| G1 (mm)   | 8.0     |
| KK        | M8x1.25 |
| L (mm)    | 7       |
| Ø MM (mm) | 8       |
| L5 (mm)   | 13      |
| L6 (mm)   | 0       |
| PL (mm)   | 9       |
| SW (mm)   | 7       |
| VD (mm)   | 3       |
| WF (mm)   | 17.0    |
| XC (mm)   | 77.0    |
| XC1 (mm)  | 62.5    |
| XC2 (mm)  | 70.8    |
| SW1 (mm)  | 19      |

|            |     |
|------------|-----|
| BG (mm)    | 0   |
| BG1 (mm)   | 0.0 |
| FB         | 0   |
| RT         | 0   |
| Ø RT1 (mm) | 0   |
| TC (mm)    | 0   |
| TF (mm)    | 0.0 |