

Compact cylinders, Multi-position versions - Series 31

Product code: 31M2A025A25/40N

Datasheet creation date: 07/03/2025 21:09

Check the most updated document online [click here](#)



TECHNICAL DATA

Series	31
Version	M=male rod thread
Operation	2 = double-acting
Materials	A = rolled stainless steel AISI 303 rod tube profile aluminium
Diameter (mm)	25
Construction	A = standard
Stages	2 = 2 stages
Stroke cylinder 1 (mm)	25
Stroke cylinder 2 (mm)	40
Stroke cylinder 3 (mm)	0
Stroke cylinder 4 (mm)	0

Compact cylinders, Multi-position versions - Series 31

Product code: 31M2A025A25/40N



DIMENSIONS

ØD (mm)	10
ØD1 (mm)	4.5
D2	M5
D3	M5
D4 (mm)	5
D5	M5
ØD8 (mm)	6
D9 (mm)	6
D10 (mm)	14
E1	M5
F (mm)	8.0
F1 (mm)	31.5
FX (mm)	12.0
H (mm)	39.1
H1 (mm)	78.0
H2 (mm)	17.0
H3 (mm)	67.0
H4 (mm)	0.0
K1	M10x1,25
L (mm)	40
L1 (mm)	26
L2 (mm)	41.5
L3 (mm)	18

L4 (mm)	15.6
T (mm)	10
T1 (mm)	22
T2 (mm)	4
SW1 (mm)	8
SWK (mm)	8