

## Compact magnetic cylinders - Series 32

Product code: 32CF2A032A300

Datasheet creation date: 20/05/2026 06:09

Check the most updated document online [click here](#)




### TECHNICAL DATA

<b>Series</b>	32
<b>Version</b>	CF = self-cushioning with female rod thread (from Ø32 to Ø100)
<b>Operation</b>	2=double-acting
<b>Materials</b>	A = anodized aluminium body, end blocks and piston,
<b>Diameter (mm)</b>	32
<b>Construction</b>	A = standard
<b>Cylinder Stroke (mm)</b>	300
<b>Seal options</b>	= standard
<b>Rod length (mm)</b>	0
<b>Rod length 2 (mm)</b>	0
<b>Certifications</b>	= standard

## Compact magnetic cylinders - Series 32

Product code: 32CF2A032A300



### DIMENSIONS

<b>A (mm)</b>	19
<b>AF (mm)</b>	13
<b>BG (mm)</b>	0.0
<b>G (mm)</b>	14.3
<b>Ø (mm)</b>	12
<b>Ø (mm)</b>	0
<b>D4 (mm)</b>	9
<b>D5 (mm)</b>	6
<b>D6 (mm)</b>	17
<b>D7</b>	M5
<b>D8 (mm)</b>	5
<b>E (mm)</b>	49.6
<b>EE</b>	G1\8
<b>H (mm)</b>	10
<b>KF</b>	M8
<b>KK</b>	M10x1,25
<b>LA (mm)</b>	0
<b>L4 (mm)</b>	28
<b>PL (mm)</b>	7.6
<b>RT</b>	M6
<b>SW1 (mm)</b>	10
<b>T2 (mm)</b>	2
<b>T3 (mm)</b>	6

<b>TG (mm)</b>	32.5
<b>ZA (mm)</b>	44.0
<b>ZB (mm)</b>	51.0
<b>ZC (mm)</b>	58