

## Compact magnetic cylinders - Series 32

Product code: 32CF2A100A050

Datasheet creation date: 20/05/2026 06:14

Check the most updated document online [click here](#)



### TECHNICAL DATA

<b>Series</b>	32
<b>Version</b>	CF = self-cushioning with female rod thread (from Ø32 to Ø100)
<b>Operation</b>	2=double-acting
<b>Materials</b>	A = anodized aluminium body, end blocks and piston,
<b>Diameter (mm)</b>	100
<b>Construction</b>	A = standard
<b>Cylinder Stroke (mm)</b>	50
<b>Seal options</b>	= standard
<b>Rod length (mm)</b>	0
<b>Rod length 2 (mm)</b>	0
<b>Certifications</b>	= standard

## Compact magnetic cylinders - Series 32

Product code: 32CF2A100A050



### DIMENSIONS

<b>A (mm)</b>	28
<b>AF (mm)</b>	20
<b>BG (mm)</b>	0.0
<b>G (mm)</b>	18
<b>Ø (mm)</b>	25
<b>Ø (mm)</b>	0
<b>D4 (mm)</b>	12
<b>D5 (mm)</b>	12
<b>D6 (mm)</b>	24
<b>D7</b>	M10
<b>D8 (mm)</b>	10
<b>E (mm)</b>	115.6
<b>EE</b>	G1/8
<b>H (mm)</b>	14
<b>KF</b>	M12
<b>KK</b>	M16x1,5
<b>LA (mm)</b>	0
<b>L4 (mm)</b>	80
<b>PL (mm)</b>	8.0
<b>RT</b>	M10
<b>SW1 (mm)</b>	22
<b>T2 (mm)</b>	4
<b>T3 (mm)</b>	10.5

<b>TG (mm)</b>	89.0
<b>ZA (mm)</b>	67.0
<b>ZB (mm)</b>	76.7
<b>ZC (mm)</b>	86.4