

## Compact magnetic cylinders - Series 32

Product code: 32F2A050A015

Datasheet creation date: 19/05/2026 08:38

Check the most updated document online [click here](#)



### TECHNICAL DATA

<b>Series</b>	32
<b>Version</b>	F=female rod thread
<b>Operation</b>	2=double-acting
<b>Materials</b>	A = anodized aluminium body, end blocks and piston,
<b>Diameter (mm)</b>	50
<b>Construction</b>	A = standard
<b>Cylinder Stroke (mm)</b>	15
<b>Seal options</b>	= standard
<b>Rod length (mm)</b>	0
<b>Rod length 2 (mm)</b>	0
<b>Certifications</b>	= standard

## Compact magnetic cylinders - Series 32

Product code: 32F2A050A015



### DIMENSIONS

<b>A (mm)</b>	22
<b>AF (mm)</b>	16
<b>BG (mm)</b>	0.0
<b>G (mm)</b>	14.3
<b>Ø (mm)</b>	16
<b>Ø (mm)</b>	0
<b>D4 (mm)</b>	12
<b>D5 (mm)</b>	10
<b>D6 (mm)</b>	22
<b>D7</b>	M6
<b>D8 (mm)</b>	6
<b>E (mm)</b>	69.6
<b>EE</b>	G1/8
<b>H (mm)</b>	12
<b>KF</b>	M10
<b>KK</b>	M12x1,25
<b>LA (mm)</b>	0
<b>L4 (mm)</b>	42
<b>PL (mm)</b>	7.6
<b>RT</b>	M8
<b>SW1 (mm)</b>	13
<b>T2 (mm)</b>	4
<b>T3 (mm)</b>	7

<b>TG (mm)</b>	46.5
<b>ZA (mm)</b>	45.0
<b>ZB (mm)</b>	53.0
<b>ZC (mm)</b>	61