

## Compact magnetic cylinders - Series 32

Product code: 32M2A063A085

Datasheet creation date: 08/03/2025 10:33

Check the most updated document online [click here](#)



### TECHNICAL DATA

|                             |   |
|-----------------------------|---|
| <b>Series</b>               | 32  |
| <b>Ø cyl. (mm)</b>          | 63  |
| <b>Version</b>              | M=male rod thread                                   |
| <b>Operation</b>            | 2=double-acting                                     |
| <b>Materials</b>            | A = anodized aluminium body, end blocks and piston, |
| <b>Construction</b>         | A = standard  |
| <b>Stroke type</b>          | V=variable  |
| <b>Stroke Cylinder (mm)</b> | 85  |
| <b>Rod seals material</b>   | Standard  |
| <b>Rod length (mm)</b>      | 0   |

## Compact magnetic cylinders - Series 32

Product code: 32M2A063A085



### DIMENSIONS

|          |          |
|----------|----------|
| A (mm)   | 22       |
| AF (mm)  | 16       |
| BG (mm)  | 0.0      |
| G (mm)   | 14       |
| Ø (mm)   | 16       |
| Ø (mm)   | 0        |
| D2 (mm)  | 45       |
| D3 (mm)  | 39       |
| D4 (mm)  | 12       |
| D5 (mm)  | 10       |
| D6 (mm)  | 22       |
| D7       | M6       |
| D8 (mm)  | 6        |
| E (mm)   | 79.6     |
| EE       | G1\8     |
| H (mm)   | 12       |
| KF       | M10      |
| KK       | M12x1,25 |
| LA (mm)  | 0        |
| L4 (mm)  | 50       |
| PL (mm)  | 7.6      |
| RT       | M8       |
| SW1 (mm) | 13       |

|         |      |
|---------|------|
| T1 (mm) | 2    |
| T2 (mm) | 4    |
| T3 (mm) | 7    |
| TG (mm) | 56.5 |
| ZA (mm) | 49.0 |
| ZB (mm) | 57.0 |
| ZC (mm) | 65   |