

Compact magnetic cylinders - Series 32

Product code: 32M2A100A120

Datasheet creation date: 08/03/2025 10:17

Check the most updated document online [click here](#)



TECHNICAL DATA

| | |
|-----------------------------|---|
| Series | 32 |
| Ø cyl. (mm) | 100 |
| Version | M=male rod thread |
| Operation | 2=double-acting |
| Materials | A = anodized aluminium body, end blocks and piston, |
| Construction | A = standard |
| Stroke type | V=variable |
| Stroke Cylinder (mm) | 120 |
| Rod seals material | Standard |
| Rod length (mm) | 0 |

Compact magnetic cylinders - Series 32

Product code: 32M2A100A120



DIMENSIONS

| | |
|-----------------|---------|
| A (mm) | 28 |
| AF (mm) | 20 |
| BG (mm) | 0.0 |
| G (mm) | 18 |
| Ø (mm) | 25 |
| Ø (mm) | 0 |
| D2 (mm) | 55 |
| D3 (mm) | 49 |
| D4 (mm) | 12 |
| D5 (mm) | 12 |
| D6 (mm) | 24 |
| D7 | M10 |
| D8 (mm) | 10 |
| E (mm) | 115.6 |
| EE | G1/8 |
| H (mm) | 14 |
| KF | M12 |
| KK | M16x1,5 |
| LA (mm) | 0 |
| L4 (mm) | 80 |
| PL (mm) | 8.0 |
| RT | M10 |
| SW1 (mm) | 22 |

| | |
|----------------|------|
| T1 (mm) | 2 |
| T2 (mm) | 4 |
| T3 (mm) | 10.5 |
| TG (mm) | 89.0 |
| ZA (mm) | 67.0 |
| ZB (mm) | 76.7 |
| ZC (mm) | 86.4 |