

## Compact magnetic cylinders - Series 32

Product code: 32M3A025A030

Datasheet creation date: 08/03/2025 10:25

Check the most updated document online [click here](#)



### TECHNICAL DATA

|                             |   |
|-----------------------------|---|
| <b>Series</b>               | 32  |
| <b>Ø cyl. (mm)</b>          | 25  |
| <b>Version</b>              | M=male rod thread                                   |
| <b>Operation</b>            | 3=double-acting through rod                         |
| <b>Materials</b>            | A = anodized aluminium body, end blocks and piston, |
| <b>Construction</b>         | A = standard  |
| <b>Stroke type</b>          | A = standard  |
| <b>Stroke Cylinder (mm)</b> | 30  |
| <b>Rod seals material</b>   | Standard  |
| <b>Rod length (mm)</b>      | 0   |

## Compact magnetic cylinders - Series 32

Product code: 32M3A025A030



### DIMENSIONS

|          |      |
|----------|------|
| A (mm)   | 16   |
| AF (mm)  | 11   |
| BG (mm)  | 20.0 |
| G (mm)   | 11.9 |
| Ø (mm)   | 10   |
| Ø (mm)   | 9    |
| D2 (mm)  | 0    |
| D3 (mm)  | 0    |
| D4 (mm)  | 9    |
| D5 (mm)  | 6    |
| D6 (mm)  | 14   |
| D7       | M5   |
| D8 (mm)  | 5    |
| E (mm)   | 40.7 |
| EE       | M5   |
| H (mm)   | 8    |
| KF       | M6   |
| KK       | M8   |
| LA (mm)  | 5    |
| L4 (mm)  | 22   |
| PL (mm)  | 7.0  |
| RT       | M5   |
| SW1 (mm) | 8    |

|         |      |
|---------|------|
| T1 (mm) | 0    |
| T2 (mm) | 2    |
| T3 (mm) | 6.5  |
| TG (mm) | 26.0 |
| ZA (mm) | 38.8 |
| ZB (mm) | 44.5 |
| ZC (mm) | 50.2 |