

Compact magnetic cylinders - Series 32

Product code: 32M3A125A230

Datasheet creation date: 08/03/2025 10:19

Check the most updated document online [click here](#)



TECHNICAL DATA

Series	32
Ø cyl. (mm)	125
Version	M=male rod thread
Operation	3=double-acting through rod
Materials	A = anodized aluminium body, end blocks and piston,
Construction	A = standard
Stroke type	V=variable
Stroke Cylinder (mm)	230
Rod seals material	Standard
Rod length (mm)	0

Compact magnetic cylinders - Series 32

Product code: 32M3A125A230



DIMENSIONS

A (mm)	40
AF (mm)	25
BG (mm)	20.0
G (mm)	20
Ø (mm)	25
Ø (mm)	0
D2 (mm)	60
D3 (mm)	50
D4 (mm)	12
D5 (mm)	12
D6 (mm)	0
D7	M10
D8 (mm)	10
E (mm)	134.6
EE	G1/4
H (mm)	14
KF	M16
KK	M20x1,5
LA (mm)	8
L4 (mm)	80
PL (mm)	10.5
RT	M10
SW1 (mm)	22

T1 (mm)	4
T2 (mm)	4
T3 (mm)	10.5
TG (mm)	110.0
ZA (mm)	81.0
ZB (mm)	92.0
ZC (mm)	103