

Cylinders ISO 15552 (ex DIN/ISO 6431 / VDMA 24562) - Series 40K

Product code: 40K2L320A0640

Datasheet creation date: 08/03/2025 11:01

Check the most updated document online [click here](#)



TECHNICAL DATA

Series (mm)	40
Version	K = standard, magnetic
Operation	2 = double-acting (front and rear cushions)
Materials	L = rolled stainless steel rod AISI 420B anodized aluminium round tube NBR seals
Ø (mm)	320
Construction	A = standard
Stroke type	variable
Stroke (mm)	640
Option	Standard
extended piston (mm)	0
Certifications	Standard

Cylinders ISO 15552 (ex DIN/ISO 6431 / VDMA 24562) - Series 40K

Product code: 40K2L320A0640



DIMENSIONS

Ø (mm)	63
KK	M48x2
Ø D11 (mm)	110
PL (mm)	30.0
G (mm)	35
L1 (mm)	90
AM (mm)	96
VA (mm)	10
EE	G1
WH (mm)	120
L2 (mm)	340.000
ZJ (mm)	340
VD (mm)	12
N (mm)	55.5
RT	M24
BG (mm)	28
TG (mm)	270
E (mm)	350
SW1 (mm)	55
SW3 (mm)	6
SW4 (mm)	75
Cushioning stroke (mm)	50
XV1±2 (mm)	210

XV2±2 (mm)	230
XV3±2 (mm)	250
h14 (mm)	400
TK (mm)	70
e9 (mm)	50
h14 (mm)	50
UW (mm)	400
R (mm)	0.0