

## Cylinders ISO 15552 (ex DIN/ISO 6431 / VDMA 24562) - Series 40K

Product code: 40K2L320A0650

Datasheet creation date: 08/03/2025 11:01

Check the most updated document online [click here](#)



### TECHNICAL DATA

<b>Series (mm)</b>	40
<b>Version</b>	K = standard, magnetic
<b>Operation</b>	2 = double-acting (front and rear cushions)
<b>Materials</b>	L = rolled stainless steel rod AISI 420B anodized aluminium round tube NBR seals
<b>Ø (mm)</b>	320
<b>Construction</b>	A = standard
<b>Stroke type</b>	variable
<b>Stroke (mm)</b>	650
<b>Option</b>	Standard
<b>extended piston (mm)</b>	0
<b>Certifications</b>	Standard

## Cylinders ISO 15552 (ex DIN/ISO 6431 / VDMA 24562) - Series 40K

Product code: 40K2L320A0650



### DIMENSIONS

Ø (mm)	63
KK	M48x2
Ø D11 (mm)	110
PL (mm)	30.0
G (mm)	35
L1 (mm)	90
AM (mm)	96
VA (mm)	10
EE	G1
WH (mm)	120
L2 (mm)	340.000
ZJ (mm)	340
VD (mm)	12
N (mm)	55.5
RT	M24
BG (mm)	28
TG (mm)	270
E (mm)	350
SW1 (mm)	55
SW3 (mm)	6
SW4 (mm)	75
Cushioning stroke (mm)	50
XV1±2 (mm)	210

XV2±2 (mm)	230
XV3±2 (mm)	250
h14 (mm)	400
TK (mm)	70
e9 (mm)	50
h14 (mm)	50
UW (mm)	400
R (mm)	0.0