

Cylinders ISO 15552 (ex DIN/ISO 6431 / VDMA 24562) - Series 40K

Product code: 40K2T160A0200

Datasheet creation date: 08/03/2025 10:51

Check the most updated document online [click here](#)



TECHNICAL DATA

| | |
|-----------------------------|--|
| Series (mm) | 40 |
| Version | K = standard, magnetic |
| Operation | 2 = double-acting (front and rear cushions) |
| Materials | T = stainless steel AISI 420B tie-rods - stainless steel AISI 303 tie-rod nuts |
| Ø (mm) | 160 |
| Construction | A = standard |
| Stroke type | standard |
| Stroke (mm) | 200 |
| Option | Standard |
| extended piston (mm) | 0 |
| Certifications | Standard |

Cylinders ISO 15552 (ex DIN/ISO 6431 / VDMA 24562) - Series 40K

Product code: 40K2T160A0200



DIMENSIONS

| | |
|------------------------|---------|
| Ø (mm) | 40 |
| KK | M36x2 |
| Ø D11 (mm) | 65 |
| PL (mm) | 25.5 |
| G (mm) | 15 |
| L1 (mm) | 55 |
| AM (mm) | 72 |
| VA (mm) | 6 |
| EE | G3/4 |
| WH (mm) | 80 |
| L2 (mm) | 260.000 |
| ZJ (mm) | 260 |
| VD (mm) | 6 |
| N (mm) | 45.0 |
| RT | M16 |
| BG (mm) | 24 |
| TG (mm) | 140 |
| E (mm) | 180 |
| SW1 (mm) | 36 |
| SW3 (mm) | 4 |
| SW4 (mm) | 55 |
| Cushioning stroke (mm) | 33 |
| XV1±2 (mm) | 145 |

| | |
|------------|-----|
| XV2±2 (mm) | 170 |
| XV3±2 (mm) | 195 |
| h14 (mm) | 200 |
| TK (mm) | 40 |
| e9 (mm) | 32 |
| h14 (mm) | 32 |
| UW (mm) | 200 |
| R (mm) | 0.2 |