

## Cylinders Series 42 - Series 42

Product code: 42M2N040A0200

Datasheet creation date: 08/03/2025 11:15

Check the most updated document online [click here](#)



### TECHNICAL DATA

|                      |                                                                             |
|----------------------|-----------------------------------------------------------------------------|
| <b>Series</b>        | 42                                                                          |
| <b>Diameter (mm)</b> | 40                                                                          |
| <b>Version</b>       | M = standard magnetic                                                       |
| <b>Operation</b>     | 2 = double-acting (front and rear cushions)                                 |
| <b>Materials</b>     | N = rod stainless steel AISI 420B; tube stainless steel AISI 304; NBR seals |
| <b>Construction</b>  | A = standard (screw with ring V+ lock for nut for rod U)                    |
| <b>Stroke type</b>   | standard                                                                    |
| <b>Stroke (mm)</b>   | 200                                                                         |

## Cylinders Series 42 - Series 42

Product code: 42M2N040A0200



### DIMENSIONS

|          |          |
|----------|----------|
| Ø A (mm) | 16       |
| KK       | M12x1.25 |
| B        | M38x1.5  |
| B1 (mm)  | 10       |
| B2 (mm)  | 50.0     |
| B3 (mm)  | 30.0     |
| B4 (mm)  | 43       |
| C        | G1\4     |
| Ø D (mm) | 38       |
| D1 (mm)  | 46       |
| D2       | M10x1    |
| D3 (mm)  | 50       |
| E (mm)   | 29.0     |
| F (mm)   | 15.0     |
| G (mm)   | 5.0      |
| SW1 (mm) | 13       |
| SW2 (mm) | 19       |
| AM (mm)  | 24       |
| WH (mm)  | 30       |
| L (mm)   | 175      |
| L1 (mm)  | 135      |
| L2 (mm)  | 105      |
| L3 (mm)  | 54       |

|                             |    |
|-----------------------------|----|
| L4 (mm)                     | 22 |
| L5 (mm)                     | 19 |
| L6 (mm)                     | 13 |
| L7 (mm)                     | 16 |
| Cushion stroke front spring | 20 |
| Cushion stroke rear spring  | 17 |