

## Cylinders Series 42 - Series 42

Product code: 42M3N032A0025

Datasheet creation date: 08/03/2025 11:11

Check the most updated document online [click here](#)



### TECHNICAL DATA

|                      |   |
|----------------------|---|
| <b>Series</b>        | 42  |
| <b>Diameter (mm)</b> | 32  |
| <b>Version</b>       | M = standard magnetic   |
| <b>Operation</b>     | 3 = double-acting (no cushion)  |
| <b>Materials</b>     | N = rod stainless steel AISI 420B; tube stainless steel AISI 304; NBR seals |
| <b>Construction</b>  | A = standard (screw with ring V+ lock for nut for rod U)                    |
| <b>Stroke type</b>   | standard  |
| <b>Stroke (mm)</b>   | 25  |

## Cylinders Series 42 - Series 42

Product code: 42M3N032A0025



### DIMENSIONS

|          |          |
|----------|----------|
| Ø A (mm) | 12       |
| KK       | M10x1.25 |
| B        | M30x1.5  |
| B1 (mm)  | 8        |
| B2 (mm)  | 41.5     |
| B3 (mm)  | 28.0     |
| B4 (mm)  | 36       |
| C        | G1\8     |
| Ø D (mm) | 30       |
| D1 (mm)  | 38       |
| D2       | M8x1     |
| D3 (mm)  | 42       |
| E (mm)   | 23.5     |
| F (mm)   | 10.5     |
| G (mm)   | 5.0      |
| SW1 (mm) | 10       |
| SW2 (mm) | 17       |
| AM (mm)  | 22       |
| WH (mm)  | 26       |
| L (mm)   | 156      |
| L1 (mm)  | 120      |
| L2 (mm)  | 94       |
| L3 (mm)  | 48       |

|                             |    |
|-----------------------------|----|
| L4 (mm)                     | 18 |
| L5 (mm)                     | 15 |
| L6 (mm)                     | 11 |
| L7 (mm)                     | 14 |
| Cushion stroke front spring | 17 |
| Cushion stroke rear spring  | 12 |