

3/2-way solenoid valve, G1/4, monostable - Series 4

Product code: 434-015-22IL

Datasheet creation date: 10/03/2025 11:58

Check the most updated document online [click here](#)



TECHNICAL DATA

Mod.	434-015-22
Function	3/2 NC
Flow rate (NI/min)	1250
Operating pressure	2.5 ÷ 10
Type of manual override	IL = bistable, lever type (available on demand)
Dimensions of the solenoid	No solenoid
Solenoid voltage	

