

## Anti-rotation guide units - Series 45

Product code: 45NHB020A0010

Datasheet creation date: 10/03/2025 02:16

Check the most updated document online [click here](#)



### TECHNICAL DATA

|                      |   |
|----------------------|---|
| <b>Series</b>        | 45  |
| <b>Diameter (mm)</b> | 20  |
| <b>Version</b>       | N = standard  |
| <b>Operation</b>     | HB = "H" ball guide                                     |
| <b>Materials</b>     | A = anodized aluminium body, hardened steel columns C50 |
| <b>Stroke (mm)</b>   | 10  |

## Anti-rotation guide units - Series 45

Product code: 45NHB020A0010



### DIMENSIONS

|          |       |
|----------|-------|
| TF (mm)  | 68    |
| TG (mm)  | 40.0  |
| TH (mm)  | 38.0  |
| TI (mm)  | 58    |
| TM (mm)  | 20    |
| TL (mm)  | 32.5  |
| TN (mm)  | 23    |
| UF1 (mm) | 79    |
| UF (mm)  | 76    |
| G1 (mm)  | 32    |
| A (mm)   | 10    |
| WH (mm)  | 17    |
| C1 (mm)  | 108   |
| H (mm)   | 4     |
| W (mm)   | 22    |
| C (mm)   | 12    |
| K (mm)   | 58    |
| L (mm)   | 160.0 |
| L1 (mm)  | 15    |
| L2 (mm)  | 37.0  |
| L3 (mm)  | 34    |
| L4 (mm)  | 37    |
| L5 (mm)  | 71.0  |

|          |      |
|----------|------|
| L6 (mm)  | 65.0 |
| L7 (mm)  | 8.5  |
| L8 (mm)  | 0    |
| P        | M5   |
| P1       | M6   |
| T (mm)   | 14   |
| EA (mm)  | 6.5  |
| EB (mm)  | 11   |
| EC (mm)  | 6.8  |
| FA (mm)  | 5.5  |
| FB (mm)  | 10.0 |
| FC (mm)  | 5.7  |
| SW1 (mm) | 13   |
| SW2 (mm) | 13   |
| SW3 (mm) | 4    |