

Anti-rotation guide units - Series 45

Product code: 45NHB032A1200

Datasheet creation date: 10/03/2025 02:20

Check the most updated document online [click here](#)



TECHNICAL DATA

Series	45
Diameter (mm)	32
Version	N = standard
Operation	HB = "H" ball guide
Materials	A = anodized aluminium body, hardened steel columns C50
Stroke (mm)	1200

Anti-rotation guide units - Series 45

Product code: 45NHB032A1200



DIMENSIONS

TF (mm)	78
TG (mm)	32.5
TH (mm)	61.0
TI (mm)	74
TM (mm)	0
TL (mm)	0.0
TN (mm)	0
UF1 (mm)	97
UF (mm)	90
G1 (mm)	45
A (mm)	12
WH (mm)	17
C1 (mm)	125
H (mm)	6
W (mm)	17
C (mm)	12
K (mm)	76
L (mm)	177.0
L1 (mm)	4
L2 (mm)	50.2
L3 (mm)	50
L4 (mm)	37
L5 (mm)	94.0

L6 (mm)	64.0
L7 (mm)	0.0
L8 (mm)	0
P	M6
P1	-
T (mm)	14
EA (mm)	0.0
EB (mm)	0
EC (mm)	0.0
FA (mm)	6.5
FB (mm)	11.0
FC (mm)	6.8
SW1 (mm)	13
SW2 (mm)	17
SW3 (mm)	6