

Anti-rotation guide units - Series 45

Product code: 45NHB040A0225

Datasheet creation date: 10/03/2025 02:21

Check the most updated document online [click here](#)



TECHNICAL DATA

Series	45
Diameter (mm)	40
Version	N = standard
Operation	HB = "H" ball guide
Materials	A = anodized aluminium body, hardened steel columns C50
Stroke (mm)	225

Anti-rotation guide units - Series 45

Product code: 45NHB040A0225



DIMENSIONS

TF (mm)	84
TG (mm)	38.0
TH (mm)	69.0
TI (mm)	87
TL (mm)	0.0
UF1 (mm)	115
UF (mm)	110
G1 (mm)	54
A (mm)	16
WH (mm)	21
C1 (mm)	140
H (mm)	7
W (mm)	22
C (mm)	12
L (mm)	192.0
L1 (mm)	11
L2 (mm)	58.2
L3 (mm)	58
L4 (mm)	37
L5 (mm)	105.0
P	M6
FB (mm)	11.0
SW1 (mm)	15

SW2 (mm)	19
SW3 (mm)	6