

Anti-rotation guide units - Series 45

Product code: 45NHB063A1200

Datasheet creation date: 10/03/2025 02:25

Check the most updated document online [click here](#)



TECHNICAL DATA

Series	45
Diameter (mm)	63
Version	N = standard
Operation	HB = "H" ball guide
Materials	A = anodized aluminium body, hardened steel columns C50
Stroke (mm)	1200

Anti-rotation guide units - Series 45

Product code: 45NHB063A1200



DIMENSIONS

TF (mm)	105
TG (mm)	56.5
TH (mm)	100.0
TI (mm)	119
TM (mm)	0
TL (mm)	0.0
TN (mm)	0
UF1 (mm)	152
UF (mm)	145
G1 (mm)	80
A (mm)	20
WH (mm)	26
C1 (mm)	178
H (mm)	8
W (mm)	26
C (mm)	15
K (mm)	111
L (mm)	237.0
L1 (mm)	15
L2 (mm)	85.2
L3 (mm)	85
L4 (mm)	37
L5 (mm)	121.0

L6 (mm)	89.0
L7 (mm)	0.0
L8 (mm)	0
P	M8
P1	-
T (mm)	16
EA (mm)	0.0
EB (mm)	0
EC (mm)	0.0
FA (mm)	9.0
FB (mm)	15.0
FC (mm)	9.0
SW1 (mm)	22
SW2 (mm)	24
SW3 (mm)	6