

## Anti-rotation guide units - Series 45

Product code: 45NHT025A0025

Datasheet creation date: 10/03/2025 02:04

Check the most updated document online [click here](#)



### TECHNICAL DATA

|                      |  |
|----------------------|--|
| <b>Series</b>        | 45   |
| <b>Diameter (mm)</b> | 25   |
| <b>Version</b>       | N = standard   |
| <b>Operation</b>     | HT = "H" self lubricating guide                                |
| <b>Materials</b>     | A = anodized aluminium body, stainless steel columns AISI 420B |
| <b>Stroke (mm)</b>   | 25   |

## Anti-rotation guide units - Series 45

Product code: 45NHT025A0025



### DIMENSIONS

|          |       |
|----------|-------|
| TF (mm)  | 68    |
| TG (mm)  | 40.0  |
| TH (mm)  | 38.0  |
| TI (mm)  | 58    |
| TM (mm)  | 20    |
| TL (mm)  | 32.5  |
| TN (mm)  | 23    |
| UF1 (mm) | 79    |
| UF (mm)  | 76    |
| G1 (mm)  | 32    |
| A (mm)   | 10    |
| WH (mm)  | 17    |
| C1 (mm)  | 108   |
| H (mm)   | 6     |
| W (mm)   | 17    |
| C (mm)   | 12    |
| K (mm)   | 58    |
| L (mm)   | 160.0 |
| L1 (mm)  | 15    |
| L2 (mm)  | 37.0  |
| L3 (mm)  | 34    |
| L4 (mm)  | 37    |
| L5 (mm)  | 76.0  |

|          |      |
|----------|------|
| L6 (mm)  | 65.0 |
| L7 (mm)  | 8.5  |
| L8 (mm)  | 0    |
| P        | M5   |
| P1       | M6   |
| T (mm)   | 14   |
| EA (mm)  | 6.5  |
| EB (mm)  | 11   |
| EC (mm)  | 6.8  |
| FA (mm)  | 5.5  |
| FB (mm)  | 10.0 |
| FC (mm)  | 5.7  |
| SW1 (mm) | 13   |
| SW2 (mm) | 17   |
| SW3 (mm) | 6    |