

Anti-rotation guide units - Series 45

Product code: 45NHT032A1000

Datasheet creation date: 10/03/2025 02:08

Check the most updated document online [click here](#)



TECHNICAL DATA

| | |
|----------------------|--|
| Series | 45 |
| Diameter (mm) | 32 |
| Version | N = standard |
| Operation | HT = "H" self lubricating guide |
| Materials | A = anodized aluminium body, stainless steel columns AISI 420B |
| Stroke (mm) | 1000 |

Anti-rotation guide units - Series 45

Product code: 45NHT032A1000



DIMENSIONS

| | |
|----------|-------|
| TF (mm) | 78 |
| TG (mm) | 32.5 |
| TH (mm) | 61.0 |
| TI (mm) | 74 |
| TL (mm) | 0.0 |
| UF1 (mm) | 97 |
| UF (mm) | 90 |
| G1 (mm) | 45 |
| A (mm) | 12 |
| WH (mm) | 17 |
| C1 (mm) | 125 |
| H (mm) | 6 |
| W (mm) | 17 |
| C (mm) | 12 |
| L (mm) | 177.0 |
| L1 (mm) | 4 |
| L2 (mm) | 50.2 |
| L3 (mm) | 50 |
| L4 (mm) | 37 |
| L5 (mm) | 94.0 |
| P | M6 |
| FB (mm) | 11.0 |
| SW1 (mm) | 13 |

| | |
|----------|----|
| SW2 (mm) | 17 |
| SW3 (mm) | 6 |