

Anti-rotation guide units - Series 45

Product code: 45NHT040A0527

Datasheet creation date: 10/03/2025 02:09

Check the most updated document online [click here](#)



TECHNICAL DATA

| | |
|----------------------|--|
| Series | 45 |
| Diameter (mm) | 40 |
| Version | N = standard |
| Operation | HT = "H" self lubricating guide |
| Materials | A = anodized aluminium body, stainless steel columns AISI 420B |
| Stroke (mm) | 527 |

Anti-rotation guide units - Series 45

Product code: 45NHT040A0527



DIMENSIONS

| | |
|----------|-------|
| TF (mm) | 84 |
| TG (mm) | 38.0 |
| TH (mm) | 69.0 |
| TI (mm) | 87 |
| TL (mm) | 0.0 |
| UF1 (mm) | 115 |
| UF (mm) | 110 |
| G1 (mm) | 54 |
| A (mm) | 16 |
| WH (mm) | 21 |
| C1 (mm) | 140 |
| H (mm) | 7 |
| W (mm) | 22 |
| C (mm) | 12 |
| L (mm) | 192.0 |
| L1 (mm) | 11 |
| L2 (mm) | 58.2 |
| L3 (mm) | 58 |
| L4 (mm) | 37 |
| L5 (mm) | 105.0 |
| P | M6 |
| FB (mm) | 11.0 |
| SW1 (mm) | 15 |

| | |
|----------|----|
| SW2 (mm) | 19 |
| SW3 (mm) | 6 |