

Anti-rotation guide units - Series 45

Product code: 45NHT050A0125

Datasheet creation date: 10/03/2025 02:10

Check the most updated document online [click here](#)



TECHNICAL DATA

| | |
|----------------------|--|
| Series | 45 |
| Diameter (mm) | 50 |
| Version | N = standard |
| Operation | HT = "H" self lubricating guide |
| Materials | A = anodized aluminium body, stainless steel columns AISI 420B |
| Stroke (mm) | 125 |

Anti-rotation guide units - Series 45

Product code: 45NHT050A0125



DIMENSIONS

| | |
|----------|-------|
| TF (mm) | 100 |
| TG (mm) | 46.5 |
| TH (mm) | 85.0 |
| TI (mm) | 104 |
| TL (mm) | 0.0 |
| UF1 (mm) | 137 |
| UF (mm) | 130 |
| G1 (mm) | 63 |
| A (mm) | 20 |
| WH (mm) | 26 |
| C1 (mm) | 149 |
| H (mm) | 8 |
| W (mm) | 26 |
| C (mm) | 15 |
| L (mm) | 205.0 |
| L1 (mm) | 20 |
| L2 (mm) | 70.2 |
| L3 (mm) | 70 |
| L4 (mm) | 38 |
| L5 (mm) | 106.0 |
| P | M8 |
| FB (mm) | 15.0 |
| SW1 (mm) | 22 |

| | |
|----------|----|
| SW2 (mm) | 24 |
| SW3 (mm) | 6 |