

## Anti-rotation guide units - Series 45

Product code: 45NHT050A0450

Datasheet creation date: 10/03/2025 02:11

Check the most updated document online [click here](#)



### TECHNICAL DATA

|                      |  |
|----------------------|--|
| <b>Series</b>        | 45   |
| <b>Diameter (mm)</b> | 50   |
| <b>Version</b>       | N = standard   |
| <b>Operation</b>     | HT = "H" self lubricating guide                                |
| <b>Materials</b>     | A = anodized aluminium body, stainless steel columns AISI 420B |
| <b>Stroke (mm)</b>   | 450  |

## Anti-rotation guide units - Series 45

Product code: 45NHT050A0450



### DIMENSIONS

|          |       |
|----------|-------|
| TF (mm)  | 100   |
| TG (mm)  | 46.5  |
| TH (mm)  | 85.0  |
| TI (mm)  | 104   |
| TL (mm)  | 0.0   |
| UF1 (mm) | 137   |
| UF (mm)  | 130   |
| G1 (mm)  | 63    |
| A (mm)   | 20    |
| WH (mm)  | 26    |
| C1 (mm)  | 149   |
| H (mm)   | 8     |
| W (mm)   | 26    |
| C (mm)   | 15    |
| L (mm)   | 205.0 |
| L1 (mm)  | 20    |
| L2 (mm)  | 70.2  |
| L3 (mm)  | 70    |
| L4 (mm)  | 38    |
| L5 (mm)  | 106.0 |
| P        | M8    |
| FB (mm)  | 15.0  |
| SW1 (mm) | 22    |

|          |    |
|----------|----|
| SW2 (mm) | 24 |
| SW3 (mm) | 6  |