

Anti-rotation guide units - Series 45

Product code: 45NUT020A0125

Datasheet creation date: 10/03/2025 01:54

Check the most updated document online [click here](#)



TECHNICAL DATA

Series	45
Diameter (mm)	20
Version	N = standard
Operation	UT = "U" self lubricating guide
Materials	A = anodized aluminium body, stainless steel columns AISI 420B
Stroke (mm)	125

Anti-rotation guide units - Series 45

Product code: 45NUT020A0125



DIMENSIONS

TF (mm)	70
TG (mm)	55.0
TH (mm)	46.5
TI (mm)	74
TM (mm)	0
TL (mm)	32.0
TN (mm)	0
UF1 (mm)	100
UF (mm)	90
G1 (mm)	38
A (mm)	10
WH (mm)	30
C1 (mm)	48
H (mm)	4
W (mm)	22
C (mm)	12
K (mm)	15
L (mm)	77.0
L1 (mm)	71
L2 (mm)	17.0
L3 (mm)	8
L4 (mm)	48
L5 (mm)	40.0

L6 (mm)	8.5
L7 (mm)	10.0
L8 (mm)	24
P	M6
P1	M8
T (mm)	0
EA (mm)	9.0
EB (mm)	15
EC (mm)	9.0
FA (mm)	6.5
FB (mm)	11.0
FC (mm)	6.8
SW1 (mm)	13
SW2 (mm)	13
SW3 (mm)	6