

Anti-rotation guide units - Series 45

Product code: 45NUT100A0125

Datasheet creation date: 10/03/2025 01:52

Check the most updated document online [click here](#)




TECHNICAL DATA

Series	45
Diameter (mm)	100
Version	N = standard
Operation	UT = "U" self lubricating guide
Materials	A = anodized aluminium body, stainless steel columns AISI 420B
Stroke (mm)	125

Anti-rotation guide units - Series 45

Product code: 45NUT100A0125



DIMENSIONS

TF (mm)	150
TG (mm)	89.0
TH (mm)	150.0
TI (mm)	150
TM (mm)	0
TL (mm)	70.0
TN (mm)	0
UF1 (mm)	185
UF (mm)	175
G1 (mm)	110
A (mm)	20
WH (mm)	39
C1 (mm)	110
H (mm)	9
W (mm)	32
C (mm)	16
K (mm)	0
L (mm)	190.0
L1 (mm)	138
L2 (mm)	10.5
L3 (mm)	72
L4 (mm)	118
L5 (mm)	20.0

L6 (mm)	0.0
L7 (mm)	0.0
L8 (mm)	0
P	M10
P1	-
T (mm)	0
EA (mm)	0.0
EB (mm)	0
EC (mm)	0.0
FA (mm)	0.0
FB (mm)	11.0
FC (mm)	0.0
SW1 (mm)	27
SW2 (mm)	30
SW3 (mm)	6