

## Rodless cylinders - Series 50

Product code: 50M2P32A1771

Datasheet creation date: 08/03/2025 11:56

Check the most updated document online [click here](#)



### TECHNICAL DATA

|                          |   |
|--------------------------|---|
| <b>Series</b>            | 50  |
| <b>Version</b>           | M = magnetic standard   |
| <b>Operation</b>         | 2 = double-acting cushioned   |
| <b>Materials</b>         | P = anodized AL profile tube, NBR and Polyurethane seals, standard carriage |
| <b>Diameter (mm)</b>     | 32  |
| <b>Construction (mm)</b> | A = standard  |
| <b>Stroke (mm)</b>       | 1771  |

## Rodless cylinders - Series 50

Product code: 50M2P32A1771



### DIMENSIONS

|         |      |
|---------|------|
| A (mm)  | 12   |
| B (mm)  | 60   |
| C (mm)  | 90   |
| D (mm)  | 120  |
| E (mm)  | 160  |
| F       | M6   |
| F1 (mm) | 15   |
| G (mm)  | 14   |
| H (mm)  | 4.0  |
| I (mm)  | G1/4 |
| L (mm)  | 10.5 |
| L1 (mm) | 188  |
| M (mm)  | 30   |
| N (mm)  | 31   |
| P (mm)  | M6   |
| P1 (mm) | 6    |
| Q (mm)  | 15.0 |
| R (mm)  | 80.0 |
| S (mm)  | 52.0 |
| S1 (mm) | 52   |
| T (mm)  | 26.0 |
| U (mm)  | 18   |
| V (mm)  | 27   |

|          |      |
|----------|------|
| Z (mm)   | 46   |
| Y (mm)   | 48.5 |
| W (mm)   | 45   |
| AA (mm)  | 54   |
| BB (mm)  | 60   |
| TG (mm)  | 36   |
| SW2 (mm) | 6    |
| B1 (mm)  | 66   |
| B2 (mm)  | 6    |
| B3 (mm)  | 7.0  |
| B4 (mm)  | 40   |
| B5 (mm)  | 50   |
| B6 (mm)  | 160  |
| B7 (mm)  | 90   |