

## Rodless cylinders - Series 50

Product code: 50M2P50A0120

Datasheet creation date: 08/03/2025 12:05

Check the most updated document online [click here](#)



### TECHNICAL DATA

|                          |   |
|--------------------------|---|
| <b>Series</b>            | 50  |
| <b>Version</b>           | M = magnetic standard   |
| <b>Operation</b>         | 2 = double-acting cushioned   |
| <b>Materials</b>         | P = anodized AL profile tube, NBR and Polyurethane seals, standard carriage |
| <b>Diameter (mm)</b>     | 50  |
| <b>Construction (mm)</b> | A = standard  |
| <b>Stroke (mm)</b>       | 120   |

## Rodless cylinders - Series 50

Product code: 50M2P50A0120



### DIMENSIONS

|         |       |
|---------|-------|
| A (mm)  | 12    |
| B (mm)  | 70    |
| C (mm)  | 110   |
| D (mm)  | 140   |
| E (mm)  | 180   |
| F       | M6    |
| F1 (mm) | 12    |
| G (mm)  | 12    |
| H (mm)  | 4.0   |
| I (mm)  | G1/4  |
| L (mm)  | 13.5  |
| L1 (mm) | 272   |
| M (mm)  | 40    |
| N (mm)  | 39    |
| P (mm)  | M8    |
| P1 (mm) | 8     |
| Q (mm)  | 16.0  |
| R (mm)  | 103.0 |
| S (mm)  | 74.5  |
| S1 (mm) | 76    |
| T (mm)  | 38.0  |
| U (mm)  | 18    |
| V (mm)  | 28    |

|          |      |
|----------|------|
| Z (mm)   | 57   |
| Y (mm)   | 59.0 |
| W (mm)   | 85   |
| AA (mm)  | 65   |
| BB (mm)  | 69   |
| TG (mm)  | 53   |
| SW2 (mm) | 10   |
| B1 (mm)  | 74   |
| B2 (mm)  | 6    |
| B3 (mm)  | 7.0  |
| B4 (mm)  | 45   |
| B5 (mm)  | 60   |
| B6 (mm)  | 180  |
| B7 (mm)  | 100  |