

Rodless cylinders - Series 50

Product code: 50M2P50A3200

Datasheet creation date: 08/03/2025 12:10

Check the most updated document online [click here](#)



TECHNICAL DATA

| | |
|--------------------------|---|
| Series | 50 |
| Version | M = magnetic standard |
| Operation | 2 = double-acting cushioned |
| Materials | P = anodized AL profile tube, NBR and Polyurethane seals, standard carriage |
| Diameter (mm) | 50 |
| Construction (mm) | A = standard |
| Stroke (mm) | 3200 |

Rodless cylinders - Series 50

Product code: 50M2P50A3200



DIMENSIONS

| | |
|---------|-------|
| A (mm) | 12 |
| B (mm) | 70 |
| C (mm) | 110 |
| D (mm) | 140 |
| E (mm) | 180 |
| F | M6 |
| F1 (mm) | 12 |
| G (mm) | 12 |
| H (mm) | 4.0 |
| I (mm) | G1/4 |
| L (mm) | 13.5 |
| L1 (mm) | 272 |
| M (mm) | 40 |
| N (mm) | 39 |
| P (mm) | M8 |
| P1 (mm) | 8 |
| Q (mm) | 16.0 |
| R (mm) | 103.0 |
| S (mm) | 74.5 |
| S1 (mm) | 76 |
| T (mm) | 38.0 |
| U (mm) | 18 |
| V (mm) | 28 |

| | |
|----------|------|
| Z (mm) | 57 |
| Y (mm) | 59.0 |
| W (mm) | 85 |
| AA (mm) | 65 |
| BB (mm) | 69 |
| TG (mm) | 53 |
| SW2 (mm) | 10 |
| B1 (mm) | 74 |
| B2 (mm) | 6 |
| B3 (mm) | 7.0 |
| B4 (mm) | 45 |
| B5 (mm) | 60 |
| B6 (mm) | 180 |
| B7 (mm) | 100 |