

Rodless cylinders - Series 50

Product code: 50M2P63A1200

Datasheet creation date: 08/03/2025 12:12

Check the most updated document online [click here](#)



TECHNICAL DATA

| | |
|--------------------------|---|
| Series | 50 |
| Version | M = magnetic standard |
| Operation | 2 = double-acting cushioned |
| Materials | P = anodized AL profile tube, NBR and Polyurethane seals, standard carriage |
| Diameter (mm) | 63 |
| Construction (mm) | A = standard |
| Stroke (mm) | 1200 |

Rodless cylinders - Series 50

Product code: 50M2P63A1200



DIMENSIONS

| | |
|---------|-------|
| A (mm) | 16 |
| B (mm) | 90 |
| C (mm) | 140 |
| D (mm) | 180 |
| E (mm) | 220 |
| F | M8 |
| F1 (mm) | 15 |
| G (mm) | 15 |
| H (mm) | 4.0 |
| I (mm) | G3/8 |
| L (mm) | 17.5 |
| L1 (mm) | 342 |
| M (mm) | 45 |
| N (mm) | 44 |
| P (mm) | M8 |
| P1 (mm) | 8 |
| Q (mm) | 16.0 |
| R (mm) | 125.0 |
| S (mm) | 92.0 |
| S1 (mm) | 94 |
| T (mm) | 47.0 |
| U (mm) | 19 |
| V (mm) | 30 |

| | |
|----------|------|
| Z (mm) | 68 |
| Y (mm) | 70.0 |
| W (mm) | 105 |
| AA (mm) | 78 |
| BB (mm) | 83 |
| TG (mm) | 67 |
| SW2 (mm) | 10 |
| B1 (mm) | 89 |
| B2 (mm) | 7 |
| B3 (mm) | 9.0 |
| B4 (mm) | 60 |
| B5 (mm) | 80 |
| B6 (mm) | 220 |
| B7 (mm) | 130 |