

## Rodless cylinders - Series 50

Product code: 50M2P80A1470

Datasheet creation date: 08/03/2025 12:16

Check the most updated document online [click here](#)



### TECHNICAL DATA

|                          |   |
|--------------------------|---|
| <b>Series</b>            | 50  |
| <b>Version</b>           | M = magnetic standard   |
| <b>Operation</b>         | 2 = double-acting cushioned   |
| <b>Materials</b>         | P = anodized AL profile tube, NBR and Polyurethane seals, standard carriage |
| <b>Diameter (mm)</b>     | 80  |
| <b>Construction (mm)</b> | A = standard  |
| <b>Stroke (mm)</b>       | 1470  |

## Rodless cylinders - Series 50

Product code: 50M2P80A1470



### DIMENSIONS

|         |       |
|---------|-------|
| A (mm)  | 20    |
| B (mm)  | 120   |
| C (mm)  | 180   |
| D (mm)  | 240   |
| E (mm)  | 280   |
| F       | M10   |
| F1 (mm) | 20    |
| G (mm)  | 18    |
| H (mm)  | 4.0   |
| I (mm)  | G1/2  |
| L (mm)  | 32.0  |
| L1 (mm) | 408   |
| M (mm)  | 45    |
| N (mm)  | 56    |
| P (mm)  | M10   |
| P1 (mm) | 10    |
| Q (mm)  | 18.5  |
| R (mm)  | 153.5 |
| S (mm)  | 115.5 |
| S1 (mm) | 117   |
| T (mm)  | 58.5  |
| U (mm)  | 20    |
| V (mm)  | 32    |

|          |      |
|----------|------|
| Z (mm)   | 83   |
| Y (mm)   | 86.0 |
| W (mm)   | 120  |
| AA (mm)  | 95   |
| BB (mm)  | 101  |
| TG (mm)  | 83   |
| SW2 (mm) | 12   |
| B1 (mm)  | 108  |
| B2 (mm)  | 8    |
| B3 (mm)  | 11.0 |
| B4 (mm)  | 75   |
| B5 (mm)  | 100  |
| B6 (mm)  | 280  |
| B7 (mm)  | 180  |