

## Rodless cylinders - Series 50

Product code: 50M2P80A3200

Datasheet creation date: 08/03/2025 12:17

Check the most updated document online [click here](#)



### TECHNICAL DATA

<b>Series</b>	50
<b>Version</b>	M = magnetic standard
<b>Operation</b>	2 = double-acting cushioned
<b>Materials</b>	P = anodized AL profile tube, NBR and Polyurethane seals, standard carriage
<b>Diameter (mm)</b>	80
<b>Construction (mm)</b>	A = standard
<b>Stroke (mm)</b>	3200

## Rodless cylinders - Series 50

Product code: 50M2P80A3200



### DIMENSIONS

<b>A (mm)</b>	20
<b>B (mm)</b>	120
<b>C (mm)</b>	180
<b>D (mm)</b>	240
<b>E (mm)</b>	280
<b>F</b>	M10
<b>F1 (mm)</b>	20
<b>G (mm)</b>	18
<b>H (mm)</b>	4.0
<b>I (mm)</b>	G1/2
<b>L (mm)</b>	32.0
<b>L1 (mm)</b>	408
<b>M (mm)</b>	45
<b>N (mm)</b>	56
<b>P (mm)</b>	M10
<b>P1 (mm)</b>	10
<b>Q (mm)</b>	18.5
<b>R (mm)</b>	153.5
<b>S (mm)</b>	115.5
<b>S1 (mm)</b>	117
<b>T (mm)</b>	58.5
<b>U (mm)</b>	20
<b>V (mm)</b>	32

<b>Z (mm)</b>	83
<b>Y (mm)</b>	86.0
<b>W (mm)</b>	120
<b>AA (mm)</b>	95
<b>BB (mm)</b>	101
<b>TG (mm)</b>	83
<b>SW2 (mm)</b>	12
<b>B1 (mm)</b>	108
<b>B2 (mm)</b>	8
<b>B3 (mm)</b>	11.0
<b>B4 (mm)</b>	75
<b>B5 (mm)</b>	100
<b>B6 (mm)</b>	280
<b>B7 (mm)</b>	180