

## Rodless cylinders - Series 52

Product code: 52M2C50A0900

Datasheet creation date: 08/03/2025 13:22

Check the most updated document online [click here](#)



### TECHNICAL DATA

|                             |   |
|-----------------------------|---|
| <b>Series</b>               | 52M2C50A  |
| <b>Diameter (mm)</b>        | 50  |
| <b>Version</b>              | M= standard   |
| <b>Operation</b>            | 2 = double-acting, cushioned  |
| <b>Materials</b>            | C = anodized AL profile, NBR and Polyurethane seals, short carriage |
| <b>Construction</b>         | A = standard  |
| <b>Stroke Cylinder (mm)</b> | 900   |

## Rodless cylinders - Series 52

Product code: 52M2C50A0900



### DIMENSIONS

|          |       |
|----------|-------|
| W (mm)   | 105.0 |
| E (mm)   | 122.0 |
| L1 (mm)  | 210   |
| I        | G3/8  |
| B (mm)   | 35    |
| G (mm)   | 9.0   |
| N (mm)   | 30    |
| L (mm)   | 17.0  |
| Ø A (mm) | 10.0  |
| Ø X (mm) | 8.5   |
| S1 (mm)  | 94    |
| T (mm)   | 59.0  |
| Z (mm)   | 12.5  |
| C1 (mm)  | 0     |
| C (mm)   | 64    |
| U (mm)   | 34    |
| F        | M8    |
| F1 (mm)  | 16.0  |
| H (mm)   | 0.0   |
| V (mm)   | 46.0  |
| S (mm)   | 90    |
| R (mm)   | 115   |
| P        | M8    |

|         |       |
|---------|-------|
| TG (mm) | 65    |
| Q (mm)  | 17    |
| Q1 (mm) | 5     |
| T1 (mm) | 29.5  |
| T2 (mm) | 59.0  |
| T3 (mm) | 29.0  |
| T4 (mm) | 59.0  |
| L2 (mm) | 17.0  |
| L3 (mm) | 17.0  |
| D (mm)  | 10.5  |
| M (mm)  | 4.5   |
| J       | 0     |
| JP (mm) | 0.0   |
| J1 (mm) | 0     |
| R1 (mm) | 133.0 |
| X1 (mm) | 3.0   |
| Y (mm)  | 4.5   |
| Y1 (mm) | 3.0   |
| Y2 (mm) | 0     |
| Y3 (mm) | 6     |
| R2 (mm) | 0.0   |