

Rodless cylinders - Series 52

Product code: 52M2P32A0300

Datasheet creation date: 08/03/2025 13:00

Check the most updated document online [click here](#)




TECHNICAL DATA

Series	52M2P32A
Diameter (mm)	32
Version	M= standard
Operation	2 = double-acting, cushioned
Materials	P = anodized AL profile tube, NBR and Polyurethane seals, standard carriage
Construction	A = standard
Stroke Cylinder (mm)	300

Rodless cylinders - Series 52

Product code: 52M2P32A0300



DIMENSIONS

W (mm)	120.0
E (mm)	184.5
L1 (mm)	240
I	G1/8
B (mm)	25
G (mm)	5.5
N (mm)	19
L (mm)	9.5
Ø A (mm)	6.0
Ø X (mm)	5.5
S1 (mm)	58
T (mm)	32.5
Z (mm)	7.5
C1 (mm)	130
C (mm)	45
U (mm)	15
F	M5
F1 (mm)	7.0
H (mm)	100.0
V (mm)	22.0
S (mm)	54
R (mm)	69
P	M5

TG (mm)	41
Q (mm)	11
Q1 (mm)	4
T1 (mm)	17.5
T2 (mm)	34.5
T3 (mm)	17.5
T4 (mm)	34.5
L2 (mm)	9.5
L3 (mm)	9.5
D (mm)	10.5
M (mm)	4.5
J	M5
JP (mm)	0.8
J1 (mm)	9
R1 (mm)	83.8
X1 (mm)	8.0
Y (mm)	4.5
Y1 (mm)	7.0
Y2 (mm)	4
Y3 (mm)	4
R2 (mm)	81.4