

## Electromechanical cylinders - Series 6E

Product code: 6E032BS0115P10AP

Datasheet creation date: 07/03/2025 17:02

Check the most updated document online [click here](#)




### TECHNICAL DATA

<b>Series</b>	6E
<b>Size (mm)</b>	032
<b>Transmission</b>	BS = ball screw
<b>Stroke (mm)</b>	115
<b>Screw pitch (mm)</b>	P10= 10mm
<b>Construction</b>	A= standard with rod nut
<b>Extended piston rod</b>	0
<b>Version</b>	P = IP65
<b>Motor connection</b>	cylinder only
<b>Motor</b>	
<b>Brake</b>	
<b>Encoder</b>	

## Electromechanical cylinders - Series 6E

Product code: 6E032BS0115P10AP



### DIMENSIONS

AM (mm)	22
B (mm)	30
BG (mm)	16
E (mm)	46.5
F (mm)	8
F1 (mm)	0.0
F2 (mm)	0
F3 (mm)	0
KK (mm)	M10 x 1,25
(mm)	10
L1 (mm)	20
L2 (mm)	125
L3 (mm)	5.5
MM (mm)	18
N (mm)	26
R (mm)	13.0
RT (mm)	M6
PL (mm)	21
SW1 (mm)	10
SW2	G 1/8
SW3 (mm)	17
TG (mm)	32.5
VA (mm)	6

VD (mm)	4
Y	0
Y1 (mm)	0
Y2 (mm)	0
Y3 (mm)	0
WH (mm)	30
ZJ (mm)	155.0