

Guides - Series 6ENHT

Product code: 6ENHT080A0400

Datasheet creation date: 07/03/2025 15:43

Check the most updated document online [click here](#)



TECHNICAL DATA

Series	6E
Diameter (mm)	80
Version	N = standard
Operation	HT = "H" self lubricating guide
Materials	A = corpo alluminio anodizzato, colonne guida inox AISI 420B
Stroke (mm)	400

Guides - Series 6ENHT

Product code: 6ENHT080A0400



DIMENSIONS

TF (mm)	130.000
TG (mm)	72.000
TH (mm)	130.000
TI (mm)	148.000
UF1 (mm)	189.000
UF (mm)	180.000
G1 (mm)	100.000
A (mm)	25.000
WH (mm)	34.000
C1 (mm)	195.000
H (mm)	9.000
W (mm)	32.000
C (mm)	20.000
K (mm)	128.000
L (mm)	280.000
L1 (mm)	21.000
L2 (mm)	105.400
L3 (mm)	105.000
L4 (mm)	42.000
L5 (mm)	128.000
L6 (mm)	110.000
L7 (mm)	0.000
P	M10

T (mm)	20.000
FA (mm)	11.000
FB (mm)	18.000
FC (mm)	11.000
SW1 (mm)	27.000
SW2 (mm)	30.000
SW3 (mm)	6.000