

## Guides - Series 6ENHT

Product code: 6ENHT100A0400

Datasheet creation date: 07/03/2025 15:43

Check the most updated document online [click here](#)



### TECHNICAL DATA

<b>Series</b>	6E
<b>Diameter (mm)</b>	100
<b>Version</b>	N = standard
<b>Operation</b>	HT = "H" self lubricating guide
<b>Materials</b>	A = corpo alluminio anodizzato, colonne guida inox AISI 420B
<b>Stroke (mm)</b>	400

## Guides - Series 6ENHT

Product code: 6ENHT100A0400



### DIMENSIONS

TF (mm)	150.000
TG (mm)	89.000
TH (mm)	150.000
TI (mm)	172.000
UF1 (mm)	213.000
UF (mm)	200.000
G1 (mm)	120.000
A (mm)	25.000
WH (mm)	39.000
C1 (mm)	220.000
H (mm)	9.000
W (mm)	32.000
C (mm)	20.000
K (mm)	128.000
L (mm)	280.000
L1 (mm)	24.500
L2 (mm)	130.400
L3 (mm)	130.000
L4 (mm)	37.000
L5 (mm)	138.000
L6 (mm)	115.000
L7 (mm)	0.000
P	M10

T (mm)	20.000
FA (mm)	11.000
FB (mm)	18.000
FC (mm)	11.000
SW1 (mm)	27.000
SW2 (mm)	30.000
SW3 (mm)	6.000