

## Pneumatically and electropneumatically operated valves - Series 8

Product code: 810C3104-F131Y-N002FC014

Datasheet creation date: 10/03/2025 12:02

Check the most updated document online [click here](#)




### TECHNICAL DATA

<b>Series</b>	8
<b>Size</b>	10 = Size 1
<b>Body design</b>	C3 = valve with aluminium body threaded connections
<b>Number of ways - Function</b>	1 = 2/2 NC
<b>Pneumatic connections</b>	04= G1/8
<b>Orifice diameter</b>	F1= 5.0mm (T1)
<b>Seal material</b>	3 = FKM
<b>Body material</b>	1= aluminium
<b>Manual override</b>	Y = provided monostable
<b>Mounting accessories</b>	N = not provided
<b>Options</b>	00 = no option
<b>Electrical connection</b>	2F = KN in line type + protection + led - only for size 1
<b>Voltage - power consumption</b>	C014= 24V DC 1.3/0.25
<b>Version</b>	= Standard

## Pneumatically and electropneumatically operated valves - Series 8

Product code: 810C3104-F131Y-N002FC014



### DIMENSIONS

<b>Series</b>	8
<b>Size</b>	10 = Size 1
<b>Body design</b>	C3 = valve with aluminium body threaded connections
<b>Number of ways - Function</b>	1 = 2/2 NC
<b>Pneumatic connections</b>	04= G1/8
<b>Orifice diameter</b>	F1= 5.0mm (T1)
<b>Seal material</b>	3 = FKM
<b>Body material</b>	1= aluminium
<b>Manual override</b>	Y = provided monostable
<b>Mounting accessories</b>	N = not provided
<b>Options</b>	00 = no option
<b>Electrical connection</b>	2F = KN in line type + protection + led - only for size 1
<b>Voltage - power consumption</b>	C014= 24V DC 1.3/0.25
<b>Version</b>	= Standard