

## Pneumatically and electropneumatically operated valves - Series 8

Product code: 830C3406-K131Y-NPE4AC023

Datasheet creation date: 10/03/2025 12:04

Check the most updated document online [click here](#)




### TECHNICAL DATA

<b>Series</b>	8
<b>Size</b>	30 = Size 3
<b>Body design</b>	C3 = valve with aluminium body threaded connections
<b>Number of ways - Function</b>	4= 3/2 NC
<b>Pneumatic connections</b>	06= G3/8
<b>Orifice diameter</b>	K1= 9.0mm (T3)
<b>Seal material</b>	3 = FKM
<b>Body material</b>	1= aluminium
<b>Manual override</b>	Y = provided monostable
<b>Mounting accessories</b>	N = not provided
<b>Options</b>	PE = electropilot with external piloting
<b>Electrical connection</b>	4A = industrial standard (9.4 mm) - only for size 2 and 3
<b>Voltage - power consumption</b>	C023= 24V DC 2 W
<b>Version</b>	= Standard

## Pneumatically and electropneumatically operated valves - Series 8

Product code: 830C3406-K131Y-NPE4AC023



### DIMENSIONS

<b>Series</b>	8
<b>Size</b>	30 = Size 3
<b>Body design</b>	C3 = valve with aluminium body threaded connections
<b>Number of ways - Function</b>	4= 3/2 NC
<b>Pneumatic connections</b>	06= G3/8
<b>Orifice diameter</b>	K1= 9.0mm (T3)
<b>Seal material</b>	3 = FKM
<b>Body material</b>	1= aluminium
<b>Manual override</b>	Y = provided monostable
<b>Mounting accessories</b>	N = not provided
<b>Options</b>	PE = electropilot with external piloting
<b>Electrical connection</b>	4A = industrial standard (9.4 mm) - only for size 2 and 3
<b>Voltage - power consumption</b>	C023= 24V DC 2 W
<b>Version</b>	= Standard