

# Stainless steel Cylinders (DIN/ISO 6431 - Series 90

Product code: 90M2A050A0235

#### Datasheet creation date: 07/03/2025 17:18

Check the most updated document online 🖄 <u>click here</u>






### TECHNICAL DATA

Series	90
Diameter (mm)	50
Version	M = standard magnetic
Operation	2 = double-acting (front and rear cush.)
Materials	A = stainless steel AISI 316 (SS 2343), joints NBR
Construction	A = standard
Stroke type	variable
Stroke (mm)	235
rod seals viton	-



## Stainless steel Cylinders (DIN/ISO 6431 - Series 90 Product code: 90M2A050A0235



# DIMENSIONS

• (	00
A (mm)	32
B (mm)	40
BG (mm)	16
BF (mm)	12
E (mm)	65
EE	G1\4
G (mm)	31.5
кк	M16x1,5
L (mm)	106
MM (mm)	20
N (mm)	8.5
PL (mm)	21
RT (mm)	M8
R1 (mm)	74
R2 (mm)	24
SW (mm)	17
T (mm)	M8
TG (mm)	46.5
VA (mm)	4
VD (mm)	28
WH (mm)	37
ZM (mm)	180