

Stainless steel minicylinders CETOP RP52-P DIN/ISO 6432 - Series 94 e 95

Product code: 95N2A25A015

Datasheet creation date: 07/03/2025 17:30

Check the most updated document online [click here](#)



TECHNICAL DATA

| | |
|------------------------|--|
| Series | 95 |
| Diameter (mm) | 25 |
| Version | N = standard |
| Operation | 2 = double-acting (front and rear cushions) |
| Materials | A = stainless steel AISI 316 (SS 2343), joints NBR |
| Construction | A = standard |
| rod seals viton | - |
| Stroke type | variable |
| Stroke (mm) | 15 |

Stainless steel minicylinders CETOP RP52-P DIN/ISO 6432 - Series 94 e 95

Product code: 95N2A25A015



DIMENSIONS

| | |
|------------------|----------|
| A (mm) | 10 |
| AM (mm) | 22 |
| BE | M22x1,5 |
| Ø CD (mm) | 8 |
| D (mm) | 32.5 |
| EE | G1\8 |
| EW (mm) | 16 |
| KK | M10x1,25 |
| KW (mm) | 6 |
| (mm) | 5 |
| L (mm) | 12 |
| L1 (mm) | 125 |
| L2 (mm) | 64 |
| L3 (mm) | 18.5 |
| L4 (mm) | 7.5 |
| L5 (mm) | 20 |
| SW (mm) | 8 |
| WF (mm) | 28 |
| XC (mm) | 104 |