

• - Series 97

Product code: 97A2V063A0160

Datasheet creation date: 07/03/2025 17:42

Check the most updated document online [click here](#)




**TECHNICAL DATA**

<b>Series (mm)</b>	97
<b>Diameter (mm)</b>	63
<b>Version (mm)</b>	A = front end block with pin
<b>Operation (mm)</b>	2 = double-acting (front and rear cushions)
<b>Materials (mm)</b>	V = stainless steel AISI 304 - FKM seals
<b>Construction (mm)</b>	A = standard (locking ring for end cap V + lock nut for rod U)
<b>Stroke type</b>	standard
<b>Stroke (mm)</b>	160
<b>rod seal in FKM (mm)</b>	-

## • - Series 97

Product code: 97A2V063A0160



## DIMENSIONS

Ø A (mm)	20
AM (mm)	32
Ø B (mm)	-
Ø B2 (mm)	68
CB (mm)	-
CX (mm)	-
EE (mm)	G 3/8
EP (mm)	-
EX (mm)	-
EW (mm)	-
F (mm)	6
G (mm)	53
KK (mm)	M16X1,5
PL (mm)	0.0
SW (mm)	12
SW1 (mm)	24
KW1 (mm)	8
SW2 (mm)	17
U1 (mm)	40
WH	22.5
L1	158.0
L2 (mm)	135.5
L3 (mm)	95

L4	-
L7 (mm)	-
L (mm)	-
LT (mm)	-
LU (mm)	13
KW (mm)	-
Ø KV (mm)	-
XD (mm)	-
XG (mm)	45
TD (mm)	16
TL (mm)	12
UB (mm)	-
UT (mm)	104
ZC (mm)	-
Z (mm)	-