

## Proportional valve - 16mm - Series AP

Product code: AP-621L-LW3-GP75-OX2

Datasheet creation date: 20/05/2026 04:19

Check the most updated document online [click here](#)



### TECHNICAL DATA

<b>Series</b>	AP
<b>Body</b>	6= size 16mm
<b>Number of ways</b>	2= 2way
<b>Function</b>	1 = NC
<b>Connection</b>	L= barb fitting (only PVDF body)
<b>Nominal diameter (mm)</b>	L= Ø 1.6 mm
<b>Seals material</b>	W = FKM
<b>Body material</b>	3= PVDF
<b>Encapsulating material</b>	G= PA
<b>Dimensions of the solenoid (mm)</b>	P= 16x26 DIN EN 175301-803-C
<b>Solenoid voltage (V DC)</b>	7= 24 V DC 3W
<b>Coil orientation</b>	5 = fastons towards pneumatic ports/same side of the inlet
<b>Use with oxygen</b>	OX2 = for use with oxygen – cleanliness level according to ASTM G93-03 Standard Level B
<b>Kv (l/min)</b>	0.780
<b>Max pressure (bar)</b>	4.000
<b>Max flow (NI/min)</b>	52.000

