

Proportional valve- 22mm - Series AP

Product code: AP-7211-NR2-U712

Datasheet creation date: 10/03/2025 11:07

Check the most updated document online [click here](#)




TECHNICAL DATA

Series	AP
Body	7= size 22mm
Number of ways	2= 2way
Function	1= NC
Connection	1= G1/8
Nominal diameter (mm)	N= Ø 2 mm
Seals material	R= NBR
Body material	2= BRASS
Encapsulating material	U= PET
Dimensions of the solenoid (mm)	7= 22x22 DIN 43650 B
Solenoid voltage (V DC)	12= 12 V DC 6.5W
Coil orientation	= fastons opposite pneumatic doors, same output side
Version	= uncertified version
Kv (l/min)	1.700
Max pressure (bar)	5.000
Max flow (Nl/min)	135.000

Proportional valve- 22mm - Series AP

Product code: AP-7211-NR2-U712



DIMENSIONS

Series	AP
Body	7= size 22mm
Number of ways	2= 2way
Function	1= NC
Connection	1= G1/8
Nominal diameter (mm)	N= Ø 2 mm
Seals material	R= NBR
Body material	2= BRASS
Encapsulating material	U= PET
Dimensions of the solenoid (mm)	7= 22x22 DIN 43650 B
Solenoid voltage (V DC)	12= 12 V DC 6.5W
Coil orientation	= fastons opposite pneumatic doors, same output side
Version	= uncertified version
Kv (l/min)	1.700
Max pressure (bar)	5.000
Max flow (Nl/min)	135.000