

## Valves and solenoid valves - Series D (VA)

Product code: D2CVA-MR-BS

Datasheet creation date: 10/03/2025 11:19

Check the most updated document online [click here](#)



### TECHNICAL DATA

|                                |   |
|--------------------------------|---|
| <b>Series</b>                  | D   |
| <b>Size (mm)</b>               | 2 = 16 mm   |
| <b>Actuation</b>               | C = electric with M8 connection                   |
| <b>Component</b>               | VA = Valve with threaded body                     |
| <b>Type of solenoid valve</b>  | M = 5/2 Monostable                                |
| <b>Type of manual override</b> | R = with push and turn device                     |
| <b>Connection</b>              | BS = Ø6 fittings S6510 6-1/4 + silencers 2921 1/4 |

## Valves and solenoid valves - Series D (VA)

Product code: D2CVA-MR-BS

---

### **■ DIMENSIONS**

|                                |  |
|--------------------------------|--|
| <b>Series</b>                  | D  |
| <b>Size (mm)</b>               | 2 = 16 mm  |
| <b>Actuation</b>               | C = electric with M8 connection                      |
| <b>Component</b>               | VA = Valve with threaded body                        |
| <b>Type of solenoid valve</b>  | M = 5/2 Monostable                                   |
| <b>Type of manual override</b> | R = with push and turn device                        |
| <b>Connection</b>              | BS = Ø6 fittings S6510 6-1/4 +<br>silencers 2921 1/4 |